

Specifications

Eaton 10250T30G

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty Watertight/Oiltight Pushbutton, Class I Division 2, Green, Plastic Actuator, Chrome bezel, 1NO - 1NC, Non-illuminated, Flush mounting, Momentary, Flush Pushbutton

General specifications

PRODUCT NAME	Eaton 10250T pushbutton
CATALOG NUMBER	10250T30G
UPC	782113107516
PRODUCT LENGTH/DEPTH	2.4 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.2 lb
WARRANTY	1 year
COMPLIANCES	CE Marked
CERTIFICATIONS	CSA Certified UL Listed

Product specifications

TYPE	Class I division 2
ACTUATOR COLOR	Green
BEZEL	Chrome
ACTUATOR MATERIAL	Plastic
OPERATING MODE	Momentary
CONTACT CONFIGURATION	1 NO-1 NC
ILLUMINATION	Non-illuminated
SERIES	10250T
MOUNTING METHOD	Flush
	NEMA 4
	NEMA 3R
RATING	NEMA 12
	NEMA 4X
	NEMA 3
	NEMA 13
	NEMA 13
	NEMA 3
DEGREE OF PROTECTION	NEMA 4X
	NEMA 3R
	NEMA 12
	NEMA 4
PRODUCT CATEGORY	Flush pushbutton
SIZE	30.5 mm

Resources

MULTIMEDIA	How to size and select a Power Supply
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 10250T30G

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

