

Specifications



Photo is representative

Eaton 10250T849ED

Eaton 10250T pushbutton, 10250T, 30.5 mm, Class I Division 2, 40 mm, NEMA 3/3R/4/4X/12/13, NEC C1, D2, Groups B/C/D, Illum., Main. push/pull, Std, Red actuator, Plastic bus, Incand., transformer light unit, 1NO-1NC, 24 Vac/dc LUV

General specifications

PRODUCT NAME	Eaton 10250T pushbutton
CATALOG NUMBER	10250T849ED
UPC	782114518687
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT DIAMETER	2.87 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	1 year
COMPLIANCES	CE Marked FDA 3-A
CERTIFICATIONS	UL 1604 CSA Certified UL 508

Product specifications

TYPE	30.5 mm, Class I Division 2
ACTUATOR COLOR	Red
BUS MATERIAL	Plastic
ACTUATOR	Standard
OPERATING MODE	Pull: maintained Push: maintained
CONTACT CONFIGURATION	1 NO-1 NC
ILLUMINATION	Illuminated
SERIES	10250T
LEGEND	EMERGENCY STOP
LIGHT UNIT TYPE	Incandescent, transformer
LIGHT UNIT VOLTAGE	24 Vac/dc
NUMBER OF POSITIONS	2
RATING	NEMA 13 NEMA 4 NEMA 4X NEMA 3 NEC Class I Division 2, Groups B, C and D NEMA 12 NEMA 3R
SIZE	40 mm

Resources

MULTIMEDIA

[How to size and select a Power Supply](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 10250T849ED](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

