

Specifications

Photo is representative

Eaton 1270A-000

Eaton 70 Series Photoelectric Sensor Head, Photoelectric, Forward Viewing, Sensor distance: Depends on controller used, Aluminum enclosure, Thru-beam, 9 Ft. (2.7m), 0.312 diameter

General specifications

PRODUCT NAME	Eaton 70 series photoelectric sensor head
CATALOG NUMBER	1270A-000
UPC	782113822600
PRODUCT LENGTH/DEPTH	0.31 in
PRODUCT HEIGHT	1.26 in
PRODUCT WIDTH	0.31 in
PRODUCT WEIGHT	0.1375 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer

Product specifications

CABLE TYPE	Polyvinyl Chloride (PVC)
-------------------	--------------------------

ENCLOSURE MATERIAL	Aluminum
---------------------------	----------

OPERATING MODE	Thru-beam
-----------------------	-----------

SENSOR TYPE	Through beam
--------------------	--------------

SWITCH TYPE	Photoelectric
--------------------	---------------

CORD LENGTH	108 ft
--------------------	--------

OPERATING TEMPERATURE - MAX	212 °F
--	--------

OPERATING TEMPERATURE - MIN	-40 °F
--	--------

ENVIRONMENTAL RATING	NEMA 1
---------------------------------	--------

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1270A-000
--	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

