

Specifications

Photo is representative

Eaton 1273A-000

Eaton 70 Series Photoelectric Sensor Head, Photoelectric, Forward Viewing, Sensor distance: Depends on controller used, Stainless Steel enclosure, Thru-beam, 9 Ft. (2.7m)

General specifications

PRODUCT NAME	Eaton 70 series photoelectric sensor head
CATALOG NUMBER	1273A-000
UPC	782113822693
PRODUCT LENGTH/DEPTH	0.31 in
PRODUCT HEIGHT	1.26 in
PRODUCT WIDTH	0.31 in
PRODUCT WEIGHT	0.1375 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer

Product specifications

CABLE TYPE	Polyvinyl Chloride (PVC)
ENCLOSURE MATERIAL	Stainless steel
OPERATING MODE	Thru-beam
SENSOR TYPE	Through beam
SWITCH TYPE	Photoelectric
CORD LENGTH	108 ft
OPERATING TEMPERATURE - MAX	176 °F
OPERATING TEMPERATURE - MIN	-40 °F
ENVIRONMENTAL RATING	NEMA 3, NEMA 4, NEMA 6, NEMA 12, NEMA 13

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - 1273A-000](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

