

Specifications



Photo is representative



Eaton CSNRP3A3CB2401-D

Eaton Global Plus connector cable, M8, Press-on Double Ended, Right Angle Female, Straight Male, 3-pin/3-wire, 24AWG, Black cable jacket, 1m

General specifications

PRODUCT NAME	Eaton Global Plus connector cable
CATALOG NUMBER	CSNRP3A3CB2401-D
UPC	786689212070
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	0.5 lb
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

CORD LENGTH	1 m
OPERATING TEMPERATURE	-13° to 176°F (-25° to 80°C)
CABLE TYPE	Polyvinyl Chloride (PVC)
ENCLOSURE MATERIAL	PVC
CONNECTION	M8, press-on double end, RA F, STR M, 3-pole, 3-wire
CONTACT CONFIGURATION	3-pin
ENVIRONMENTAL RATING	IP67

Resources

CATALOGS

[Volume 6: Solid-State Motor Control](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CSNRP3A3CB2401-D](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

