

Specifications

Photo is representative

Eaton E29NB1

Eaton E29 pushbutton, Heavy-Duty Miniature Indicating Light, Watertight and Oiltight, Standard actuator, Incandescent, Transformer, NEMA 3, 3R, 3S, 4, 12, 13, 3-position selector switch, knob, #755, one element, NEMA 1, 240 V

General specifications

PRODUCT NAME	Eaton E29 pushbutton/indicating light
CATALOG NUMBER	E29NB1
UPC	782113134796
PRODUCT LENGTH/DEPTH	4.5 in
PRODUCT HEIGHT	1.3 in
PRODUCT WIDTH	1.1 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified UL Listed
CATALOG NOTES	Open type enclosure.

Product specifications

TYPE	17 mm, Heavy-Duty Watertight/Oiltight
LIGHT UNIT TYPE	Incandescent, transformer
PRODUCT CATEGORY	Miniature indicating light
LED LAMP NUMBER	#755
LETTER COLOR	One element
VOLTAGE RATING	240V
ENCLOSURE	NEMA 3 NEMA 3S NEMA 12 NEMA 3R NEMA 4 NEMA 13
SERIES	E29
ACTUATOR	Standard
NEMA RATING	NEMA 1
TERMINALS	Pressure

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - E29NB1
TECHNICAL DATA SHEETS	Pushbuttons and Indicating Lights - Datasheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

