

Specifications

Photo is representative

Eaton HT8CFB

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight-HT800, Pushbutton, 40 mm, NEMA 1, 2, 3, 3R, 4, 4X, 12, Non-illuminated, Three-position, Maintained push, momentary pull, Blue actuator, Mushroom, Plastic, Chrome bezel

General specifications

PRODUCT NAME	Eaton HT800 pushbutton
CATALOG NUMBER	HT8CFB
UPC	782113682426
PRODUCT LENGTH/DEPTH	2.094 in
PRODUCT HEIGHT	5.051 in
PRODUCT WIDTH	2.375 in
PRODUCT WEIGHT	1 lb
WARRANTY	1 year
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	Push-Pull
ACTUATOR COLOR	Blue
BEZEL	Chrome
BUS MATERIAL	Anodized aluminum
ENCLOSURE	NEMA 4X NEMA 2 NEMA 12 NEMA 1 NEMA 3 NEMA 4 NEMA 3R
ACTUATOR MATERIAL	Plastic
ACTUATOR	Mushroom
OPERATING MODE	Pull: momentary Push: maintained
ILLUMINATION	Non-illuminated
SERIES	HT800
NUMBER OF POSITIONS	3
DEGREE OF PROTECTION	NEMA 12 NEMA 13 NEMA 4 NEMA 3 NEMA 3R NEMA 4X
PRODUCT CATEGORY	Pushbutton
SIZE	40 mm

Resources

MULTIMEDIA	How to size and select a Power Supply
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - HT8CFB

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

