

Specifications

Photo is representative

Eaton HT8FBRV7

Eaton 30.5 mm Watertight/Oiltight Push-Pull Units, Standard
Actuator, Red, Illuminated, Red, Incandescent,
full voltage, 120 Vac/Vdc Light Unit, Two-
position, Maintained push, maintained
pull, HT800 Series

General specifications

PRODUCT NAME	Eaton HT800 pushbutton
CATALOG NUMBER	HT8FBRV7
UPC	782116303311
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	30.5 mm, Watertight/Oiltight-HT800
ENCLOSURE	NEMA 4X NEMA 3 NEMA 12 NEMA 3R NEMA 4
OPERATING MODE	Push: maintained Pull: maintained
ILLUMINATION	Illuminated
SERIES	HT800
LIGHT UNIT TYPE	Incandescent, full voltage
LIGHT UNIT VOLTAGE	120 Vac/dc
LENS COLOR	Red
NUMBER OF POSITIONS	2
RATING	NEMA 13 NEMA 3R NEMA 3 NEMA 12 NEMA 4 NEMA 4X
PRODUCT CATEGORY	Illuminated push-pull units

Resources

MULTIMEDIA

[How to size and select a Power Supply](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - HT8FBRV7](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

