

Specifications



Photo is representative



Eaton HT8JNH3A

Eaton HT800 pushbutton, 30.5 mm, Watertight/Oiltight-HT800, Selector switch unit, NEMA 3, 3R, 4, 4X, 12 and 13, Non-illuminated, Two-position, Maintained, momentary, Black actuator, Knob, Chrome bezel

General specifications

PRODUCT NAME	Eaton HT800 pushbutton
CATALOG NUMBER	HT8JNH3A
UPC	782113682891
PRODUCT LENGTH/DEPTH	2.4 in
PRODUCT HEIGHT	3.2 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified

Product specifications

TYPE	30.5 mm, Watertight/Oiltight-HT800
ACTUATOR COLOR	Black
BEZEL	Chrome
CAM CODE	Cam 3A
PRODUCT CATEGORY	Selector switch unit
ENCLOSURE	NEMA 3R NEMA 13 NEMA 4X NEMA 3 NEMA 4 NEMA 12
ACTUATOR	Knob
ILLUMINATION	Non-illuminated
OPERATING MODE	Maintained, momentary
NUMBER OF POSITIONS	2
SIZE	30 mm

Resources

MULTIMEDIA

[How to size and select a Power Supply](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - HT8|NH3A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

