

Specifications

Eaton PDB371-3



Eaton Bussmann series PDB power distribution block, IP-20 Finger-safe, 600 Vac, 600 Vdc, 310 A, Three-pole, SCCR: 200 kA (6 To 1/0 AWG), 100 kA (12 To 1/0 AWG), Panel, Tin-plated aluminum connectors

General specifications

PRODUCT NAME	Eaton Bussmann series PDB power distribution block
CATALOG NUMBER	PDB371-3
UPC	051712637831
PRODUCT LENGTH/DEPTH	5.48 in
PRODUCT HEIGHT	3.69 in
PRODUCT WIDTH	6.25 in
PRODUCT WEIGHT	2.86 lb
WARRANTY	Not Applicable
COMPLIANCES	Contact factory RoHS Compliant
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	310A
SHORT-CIRCUIT RATING	SCCR: 200 kAIC (#6-1/0 AWG), 100 kAIC (#12-1/0 AWG)
VOLTAGE RATING	600 Vac, 600 Vdc

General information

MOUNTING	Panel
SPECIAL FEATURES	IP-20 Finger-safe

Physical details

MATERIAL	Tin plated aluminum connectors
NUMBER OF POLES	Three-pole
TYPE	Power distribution block

Resources

CATALOGS	PDB371-3~POWER DISTRIBUTION BLOCK Bussmann series complete full line catalog no. 1007
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PDB371-3

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

