

SmartRack Roof-Mounted Fan Panel - 6-120V high-performance fans; 630 CFM, 5-15P plug

MODEL NUMBER: SRFANROOF



Highlights

- Roof Mount Fan Panel - 120V
- Ideal for increasing the ventilation of SmartRacks
- Features (6) 120V fans mounted in a roof panel, 6-ft. (1.83 m) cord
- Toolless mounting hardware included
- Cold rolled steel with black finish
- 2A current draw

Package Includes

- Fan panel with 6-ft. (1.83 m) power cord, mounting hardware

Description

SmartRack® SRFANROOF is ideal for increasing the ventilation in all rack enclosure server cabinets. The unit features six 120V high-performance fans mounted in a roof panel, six-foot (1.8-meter) cord with NEMA 5-15P input plug, and includes toolless mounting hardware.

COMPATIBLE SMARTRACK ENCLOSURES: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR45UB, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA and other SmartRack enclosures that specify the use of this accessory.

Features

- Ideal for increasing the ventilation in all rack enclosure server cabinets
- Unit features (6) 120V high performance fans mounted in a roof panel
- 6-ft. (1.83 m) cord with NEMA 5-15P input plug
- Includes toolless mounting hardware
- Compatible SmartRack Enclosures: SR25UB, SR25UBKD, SR25UBSP1, SR25UBTAA, SR42UB, SR42UBCL, SR42UBEXP, SR42UBG, SR42UBKD, SR42UBSP1, SR42UBTAA, SR45UB, SR48UB, SR48UBCL, SR48UBEXP, SR48UBSP1, SR42UBTAA, and other SmartRack enclosures that specify the use of this accessory

Specifications

OVERVIEW	
UPC Code	037332144546
Accessory Type	Cooling Accessories; Fan Panel
Accessory Class	Cooling Accessories
INPUT	
Nominal Input Voltage(s) Supported	120V AC



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Input Voltage Description	120V AC 50/60 Hz
Input Connection Type	NEMA 5-15P
Input Plug Features	NEMA 5-15P
Voltage Compatibility (VAC)	120
Input Frequency	50/60 Hz
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Frequency Compatibility	50 / 60 Hz
COOLING	
Cooling Type	Passive
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted ON/OFF rocker switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	15.00 x 23.25 x 37.00
Shipping Dimensions (hwd / cm)	38.10 x 59.06 x 93.98
Shipping Weight (lbs.)	34.00
Shipping Weight (kg)	15.42
Unit Dimensions (hwd / in.)	3.000 x 23.500 x 35.500
Unit Dimensions (hwd / cm)	5.33 x 55.63 x 90.17
Unit Weight (lbs.)	22
Unit Weight (kg)	9.98
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.