


Toolless Movable Waterfall Adapter Kit with 36 in. Pipe for Fiber Routing System, 130 mm

MODEL NUMBER: SRFC4WTRFL36



Movable exit maintains a proper bend radius for fiber optic cables that are routed over the side of your fiber management system.

Features

High-Impact PVC Waterfall Helps You Create Custom Fiber Cable Routing Schemes

The SmartRack® SRFC4WTRFL36 connects to a straight channel section or other fitting in your fiber routing system to allow cabling to cascade over the side. It's movable, so your fiber cables can leave or enter where needed with a proper bend radius that protects against signal loss and breakage. Made from durable, lightweight PVC material, the waterfall assembles using the included hardware to help keep your fiber optic cable bundles neat and organized. Screws tighten by hand with no tools required to complete a professional, finished look in your data center, network closet or industrial space. Corrugated plastic piping is included for guiding cabling directly into your rack.

Highlights

- Allows you flexibility in creating your custom fiber optic cable routing system
- Constructed from durable but lightweight PVC plastic
- Easy to install with your fiber routing system with no tools needed
- 36 in. corrugated PVC piping feeds cables into the top of a rack

Applications

- Create a fiber routing system along the wall or ceiling of your data center or network closet or across the tops of the rack enclosures

System Requirements

Any straight section from the SRFC family

Package Includes

- Waterfall adapter, 130 mm
- Cover
- (2) T-shaped screws
- (2) Twist nuts
- Corrugated pipe, 36 in.
- Pipe affixer
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332240880
Product Type	Waterfall
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Drop Out/Waterfall
PHYSICAL	
Color	Yellow
Shipping Dimensions (hwd / in.)	12.20 x 9.84 x 6.30
Shipping Weight (kg)	0.71



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / in.)	41.600 x 7.300 x 7.700
Unit Dimensions (hwd / cm)	105.66 x 18.54 x 19.56
Unit Weight (lbs.)	1.140
Unit Weight (kg)	0.52
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.