

## SmartRack 2U Cantilever Fixed Shelf (60 lbs / 27.2 kgs capacity; 21 in. / 533.4 mm Deep)

MODEL NUMBER: SRSHELF2PDP



### Highlights

- Fixed Shelf, 2U Cantilever mount. Required mounting hardware included
- 2 or 4 post rack compatible
- 21 inch shelf depth
- Cantilever shelf supports monitors and other equipment
- Cold rolled steel with black finish.
- Use two shelves back to back to create a deep fixed shelf in 2POST racks

### Package Includes

- Shelf and mounting hardware

### Description

The SmartRack® SRSHELF2PDP is a 2U cantilever-mount fixed shelf. Cantilever shelf supports monitors and other equipment with a 60-pound (27.2 kilograms) capacity. Shelf is compatible with 2- or 4-post rack enclosure cabinets. The SRSHELF2PDP is 21 inches in depth, but can use two shelves back to back to create a deep fixed shelf in 2-post racks. Required mounting hardware is included.

### Features

- 2U cantilever mount fixed shelf
- Cantilever shelf supports monitors and other equipment with a 60 lbs (27.2 kgs) capacity
- Shelf is compatible with 2 or 4 post rack enclosure cabinets
- SRSHELF2PDP is 21 inches in depth but can use two shelves back to back to create a deep fixed shelf in 2POST racks
- Required mounting hardware is included

## Specifications

| OVERVIEW                        |                      |
|---------------------------------|----------------------|
| UPC Code                        | 037332179333         |
| Accessory Type                  | Rack Shelves         |
| Accessory Class                 | Rack Accessories     |
| PHYSICAL                        |                      |
| Shipping Dimensions (hwd / in.) | 3.90 x 19.50 x 21.50 |
| Shipping Dimensions (hwd / cm)  | 9.91 x 49.53 x 54.61 |
| Shipping Weight (lbs.)          | 7.50                 |
| Shipping Weight (kg)            | 3.40                 |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                         |
|--------------------------------------|-------------------------|
| Unit Dimensions (hwd / in.)          | 3.500 x 19.000 x 21.000 |
| Unit Dimensions (hwd / cm)           | 8.89 x 48.26 x 45.72    |
| Unit Weight (lbs.)                   | 5                       |
| Unit Weight (kg)                     | 2.27                    |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                         |
| IP68 Rated                           | No                      |
| IP20 Rated                           | No                      |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                         |
| Product Compliance                   | RoHS; EIA/ECA-310-E     |
| <b>WARRANTY &amp; SUPPORT</b>        |                         |
| Product Warranty Period (Worldwide)  | 5-year limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.