

SmartRack Sliding Steel Rack Shelf - 1U, Vented, 28.3 in. Deep, Holds up to 50 lb. (23 kg)

MODEL NUMBER: SRSHELF4PSLVENT



Sliding rack shelf houses a wireless access point or other non-mounted device and saves space in your data center.

Features

1U Vented Sliding Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® shelf with sliding side brackets supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF4PSLVENT has a maximum load capacity of 50 pounds (22.7 kilograms). The expandable side rails support installation in racks with front-to-rear rail distances between 28 inches (71 centimeters) and 46 inches (117 centimeters).

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf mounts easily into 1U of space in a standard 4-post open frame rack or rack enclosure using the included hardware. It is 28.3 inches (72 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak.

Highlights

- Universal-mount 1U rack shelf secures non-rack equipment like WAPs and monitors
- Shelf slides in and out of the rack to allow easy access to devices and cabling
- Heavy-duty cold-rolled steel construction with maximum load capacity of 50 lb.
- Vented design maximizes airflow to protect equipment against excessive heat
- Easy to install in a standard 4-post rack using the included hardware

Package Includes

- SRSHELF4PSLVENT 1U Sliding Shelf, 28.3 in. Deep (72 cm)
- (8) M6 screws
- (8) M6 cup washers
- (8) M6 cage nuts
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332263148
Product Type	Sliding Shelf
Device Compatibility	Monitor/HDTV; Network Switch; Router
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Color	Black
Rack Height	1U



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Device Depth (cm)	116.33
Maximum Device Depth (in.)	45.8
Maximum Device Depth (mm)	1,163
Maximum Weight Capacity (lbs.)	50
Maximum Weight Capacity (kg)	23
Minimum Device Depth (cm)	71.88
Minimum Device Depth (in.)	28.3
Minimum Device Depth (mm)	719
Unit Dimensions (hwd / in.)	2.375 x 19.000 x 29.500
Unit Dimensions (hwd / cm)	4.45 x 48.21 x 76.48
Unit Weight (lbs.)	18.300
Unit Weight (kg)	8.30
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.