

Power It! 6-Outlet Power Strip, 6 ft. (1.83 m) Cord, Power Switch Cover

MODEL NUMBER: TLM606NC



Highlights

- 6 outlets
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 6-ft. (1.83 m) power cord
- Rugged metal case
- Keyhole mounting slots

Package Includes

- TLM606NC power strip
- Warranty information
- Instruction manual

Description

The Power It!® TLM606NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes six NEMA 5-15R outlets, six-foot (1.8 meters) AC power cord and keyhole mounting slots. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 6 NEMA 5-15R outlets
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 6-ft. (1.83 m) AC line cord
- Rugged metal case provides extra safety and durability
- UL certification

Specifications

OVERVIEW	
UPC Code	037332127426
INPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent switch cover snaps tight to prevent accidental shutoff
PHYSICAL	
Color	Light Gray
Material of Construction	Metal
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole slots = 203.20mm; Distance between end tabs = 330.17mm
Outlets Measurement (Center to Center)	1.62 in.
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	14.50 x 5.00 x 2.50
Shipping Dimensions (hwd / cm)	36.83 x 12.70 x 6.35
Shipping Weight (lbs.)	2.10



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	0.95
Unit Dimensions (hwd / in.)	2.000 x 13.750 x 2.750
Unit Dimensions (hwd / cm)	34.92 x 6.99 x 5.08
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91
Mounting Details	Includes flanges
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.