

Micro USB to USB OTG Host Adapter Cable, 5-Pin Micro USB B to USB A M/F, 6-in. (15.24 cm)

MODEL NUMBER: **U052-06N**



Connect a USB OTG ready Tablet or Smartphone to USB 2.0 Devices

Features

- Micro USB Male to standard USB "A" Female On-The-Go (OTG) adapter
- Plug-n-Play...No Drivers or Software required
- Connect one USB device, or add a multi-port hub for multiple USB device connections
- 6inch length allows for flexible access for attached peripherals

Specifications

OVERVIEW	
UPC Code	037332184375
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC

Highlights

- Connect Thumb Drives, Keyboards, etc to OTG Tablets and Phones
- Plug-n-Play...No Software or Drivers Required

System Requirements

- USB OTG enabled Tablet, SmartPhone, or other OTG mobile device

Package Includes

- U052-06N USB OTG Adapter



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	7.00 x 3.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 7.62 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.