

4-Port USB 2.0 Ultra-Mini Compact Hub with Power Adapter

MODEL NUMBER: **U222-004-R**



Features

- USB2.0 Hub - 4-Port
- Supports all data transfer rates up to 480Mbps
- Compact design with built-in cable (6-in.), perfect for travel
- Plug-and-play/hot-swappable allows you to add or remove a device at any time
- Diagnostic LEDs indicate power and port status
- Bus-powered or self-powered
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6ft USB-A to Micro-B USB 2.0 cable to connect the U222-004-R to the External Power Supply.
- Compatible with all major operating systems

Highlights

- Link multiple USB devices to 1 computer with ultra-compact hub
- Meets or Exceeds USB 2.0 Specifications
- Includes External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- Includes a 2.6-ft. (0.79 m) USB-A to Micro-B USB 2.0 Cable
- All four ports support USB Battery Charging (BC) specification v1.2, providing up to 1.5A for fast charging of mobile devices

Package Includes

- U222-004-R USB2.0 4-Port Ultra-Mini Hub
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A)
- USB-A to Micro-B USB 2.0 Cable, 2.6-ft. (0.79 m)

Specifications

OVERVIEW	
UPC Code	037332118127
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
INPUT	
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
POWER	
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	(4) USB A (FEMALE)
CHARGING	
Charging Ports	(4) USB-A: 5V 1.5A (7.5W)
Charging Ports Details	Any of the 4 ports
Charging Ports / Amps	(4) 1.5A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Shipping Dimensions (hwd / in.)	1.00 x 4.00 x 5.10
Shipping Dimensions (hwd / cm)	2.54 x 10.16 x 12.95
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
FEATURES & SPECIFICATIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Certifications	NOM (Mexico)
Product Compliance	RoHS; REACH; WEEE; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.