

## 7-Port USB-A Mini Hub - USB 3.x (5Gbps), International Plug Adapters

MODEL NUMBER: **U360-007-INT**



USB 3.2 Gen 1 portable hub adds 7 USB-A ports to your PC, laptop, Chromebook, tablet or other USB-enabled device.

### Features

#### USB-A Hub Connects 7 USB Peripherals to Your Computer, Laptop or Tablet

This USB mini hub connects up to seven USB peripherals to your computer, laptop, Ultrabook, Chromebook, tablet or other device with a USB-A port. It expands the potential of your device by connecting peripherals that can help you do your job faster, easier and better, such as flash drives, printers, barcode scanners, webcams, keyboards/mice, power meters and external hard drives for uploading and downloading important files.

#### Transfers Data at Fast USB 3.2 Gen 1 Speeds

All seven USB ports transfer images, video and other data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

#### Ideal for Charging Multiple Mobile Devices

The included external power supply provides 12V 3A to be shared among all seven USB ports. Each port is capable of providing up to 1.5A for fast charging of your phone, tablet, music player and other mobile devices (2.4A for Apple devices). A white LED lets you know the hub is connected and ready.

#### Ready to Use Right Out of the Package

The plug-and-play USB hub connects to your computer via the included USB cable, saving you the expense and effort of buying extra cables. It requires no drivers or other software. The included power supply comes with international plug adapters that allow you to connect to almost any AC outlet. The slim housing fits easily into a pocket, briefcase or laptop bag, so you can set up your workstation anywhere.

## Specifications

### Highlights

- Accepts up to 7 USB peripherals, turning your computer into a mini workstation
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfer
- 5V/1.5A charging ports quickly charge smartphones and other mobile devices
- Slim housing fits easily into backpack or bag for convenient work-from-anywhere use
- Plug-and-play operation with no software required for immediate connection

### System Requirements

Compatible with USB-enabled operating systems (USB 3.2 Gen 1 port needed to achieve USB 3.2 Gen 1 speeds)

### Package Includes

- U360-007-INT 7-Port USB-A Mini Hub
- USB-B to USB-A cable, 3 ft. (0.9 m)
- External power supply (Input: 100-240V, 50/60 Hz, 1.5A; Output: 12V 3A)
- (3) International plug adapters (U.K., Europe, Australia)

#### OVERVIEW

UPC Code	037332272058
Product Type	Hub



Powering Business Worldwide

TRIPP LITE  
SERIES

Technology	USB 3.x
Host Connector	USB A (MALE)
<b>VIDEO</b>	
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
<b>DATA</b>	
Data Ports	(7) USB A (FEMALE)
Data Ports Details	(7) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>INPUT</b>	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.5A
AC Power Adapter Output Specs (V / A)	12V / 3A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	6.102
Product Length (cm.)	15.5
Product Length (ft.)	0.508
Product Length (m)	0.155
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	Yes
<b>POWER</b>	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 1.5A; Output: 12V, 3A, 5 ft.
DC Barrel Plug	OD: 5.5 x 2.5 x 10mm, Positive Pin, Negative Sleeve
Power Consumption (Watts)	1.40
USB Power Delivery (PD) Charging Support	No
<b>CONNECTIONS</b>	
Number of Ports	7



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(7) USB 3.0 A (FEMALE)
Connector Plating	Nickel
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue (Power) White (Connection)
<b>CHARGING</b>	
Charging Ports	USB-A: 5V 1.5A (7.5W); 2.4A Quick Charge
Charging Ports Details	BC 1.2 Specification provides 1.5A to connected devices and 2.4A for Apple devices
Charging Ports / Amps	1.5A; 2.4A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	ABS
Unit Dimensions (hwd / in.)	0.870 x 6.100 x 2.000
Unit Dimensions (hwd / cm)	2.2 x 15.5 x 5.1
Unit Packaging Type	Box
Unit Weight (lbs.)	0.22
Unit Weight (kg)	0.10
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	28.4° to 125.6°F (-2° to 52°C)
Storage Temperature Range	-4° to 132.8°F (-20° to 56°C)
Relative Humidity	5 to 95% RH, Non-Condensing
BTUs	4.8 BTU/Hr
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A 3.0), 5V 2A (10W) Output (USB 2A Charger)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Over Current Protection	Yes
USB Hub Ports	Yes
Number of USB Hub Ports	7
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
External Power Supply Certifications	C-Tick; CCC; CE; DOE; GS; TUV; UL; WEEE; cUL



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.