

## USB-C Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), 5A (100W) Rating, Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U420-003-G2-5A**



USB-C cable provides up to 20V 5A (100W) of power—more than enough to charge large-capacity mobile devices, such as the MacBook Pro®. Also connects smartphones, computers, wall chargers and other USB-C devices.

### Features

**Connects 2 USB-C Devices** Power output up to 20V 5A (100W) for fast-charging large mobile devices, such as MacBook Pro®. Recommended for connecting smartphones, tablets, computers, wall chargers and other USB-C devices. Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps. Backward compatible with previous USB generations. Compatible with Thunderbolt 3 devices.

**Reversible USB-C Male Connectors** Fumble-free reversible plugs connect in either direction to ensure fast, easy connection every time.

**Premium Construction** Molded connectors and gold-plated contacts for maximum conductivity and minimum data loss. Foil and braid shielding delivers reliable, error-free signal quality and EMI/RFI protection.

## Specifications

| OVERVIEW             |                      |
|----------------------|----------------------|
| UPC Code             | 037332202888         |
| Technology           | Thunderbolt; USB 3.x |
| Cable Type           | Passive              |
| CONNECTIONS          |                      |
| Side A - Connector 1 | USB C (MALE)         |
| Side B - Connector 1 | USB C (MALE)         |
| Connector Plating    | Nickel               |

### Highlights

- Power output up to 5A for fast-charging large mobile devices
- Supports USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C plugs on both ends for fumble-free connection
- Error-free signal quality and EMI/RFI line noise protection
- Compatible with Thunderbolt™ 3 devices

### System Requirements

- Devices with USB-C female connectors

### Package Includes

- U420-003-G2-5A USB 3.2 Gen 2 (10 Gbps) Cable with 5A Rating, USB-C to USB-C (M/M), 3 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Contact Plating                      | Gold                                |
| Connector Style                      | Straight                            |
| <b>PHYSICAL</b>                      |                                     |
| Material of Construction             | PVC                                 |
| Cable Jacket Color                   | Black                               |
| Cable Jacket Rating                  | VW-1                                |
| Cable Outer Diameter (OD)            | 5.2MM                               |
| Cable Length (ft.)                   | 3                                   |
| Cable Length (m)                     | 0.91                                |
| Cable Length (in.)                   | 36                                  |
| Cable Length (cm)                    | 91.4                                |
| Shipping Dimensions (hwd / in.)      | 0.50 x 6.00 x 9.00                  |
| Shipping Dimensions (hwd / cm)       | 1.27 x 15.24 x 22.86                |
| Shipping Weight (lbs.)               | 0.30                                |
| Shipping Weight (kg)                 | 0.14                                |
| Unit Dimensions (hwd / in.)          | 0.500 x 6.000 x 9.000               |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)         |
| Storage Temperature Range            | -4° to 185°F (-20° to 85°C)         |
| Relative Humidity                    | 10% to 85% RH, Non-Condensing       |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| USB Specification                    | USB 3.2 Gen 2 (Up to 10 Gbps)       |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Compliance                   | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |
| Product Warranty Period (Worldwide)  | 3-year limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.