

USB-C to Gigabit Network Adapter with Right Angle USB-C, Thunderbolt 3 Compatibility - White

MODEL NUMBER: **U436-06N-GBW-RA**



Connects the USB-C or Thunderbolt 3 port on your computer, laptop, MacBook, Chromebook or tablet to a wired Gigabit Ethernet network.

Features

USB-C to Gigabit Ethernet Adapter Connects to Your Laptop's USB-C or Thunderbolt 3 Port This USB Type-C to Gigabit Ethernet NIC Network Adapter (M/F) allows your computer, tablet, laptop, notebook, MacBook, Chromebook, Ultrabook or smartphone to connect to a wired Ethernet network. Connect the right-angle USB-C connector to your device's USB-C or Thunderbolt 3 port, and connect the RJ45 port to a UTP cable (such as N201-Series, sold separately). Ideal for settings in which no Wi-Fi is available or when a wired connection offers faster speeds, this USB 3.1 Gen 1 adapter lets you enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers and audio/video streaming.

Built-In USB-C Cable Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Right-Angle USB-C Plug Makes Connecting in Tight Spaces Easier The space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Ready to Use Right Out of the Package The plug-and-play network adapter requires no software, drivers or external power. The compact unit fits easily into a pocket, briefcase or laptop bag for connecting on the go. Plug it into your laptop for instant network connection.

Specifications

OVERVIEW	
UPC Code	037332214157
INPUT	

Highlights

- Connect to a wired 10/100/1000 Mbps network where Wi-Fi is weak or unavailable
- More convenient, less expensive than installing or upgrading an internal Ethernet card
- Widely compatible with Windows, Mac and Chromium operating systems
- Right-angle USB-C plug allows easier connection in confined or hard-to-reach spaces
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Access a wired Ethernet network in a location with no or spotty Wi-Fi
- Upload data from your MacBook or download data from the Ethernet at true 10/100/1000 Mbps speeds

System Requirements

- Laptop or computer with an available USB-C port
- Ethernet network and a Cat6 cable to connect to it.

Package Includes

- U436-06N-GBW-RA Right-Angle USB-C to Gigabit Ethernet Network Adapter (M/F), White
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Built-In Cable Length (ft.)	0.328
Built-In Cable Length (m)	0.1
Built-In Cable Length (in.)	3.94
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (MALE) - RIGHT ANGLE
Side B - Connector 1	RJ45 (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Network cable connected = Green; Data transmitting = Green
PHYSICAL	
Color	White
Material of Construction	ABS, PVC
Cable Jacket Rating	VW-1
Unit Dimensions (hwd / in.)	0.630 x 6.000 x 1.060
Unit Dimensions (hwd / mm)	16 x 150 x 27
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)



Powering Business Worldwide

TRIPP LITE
SERIES

FEATURES & SPECIFICATIONS

USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
Recommended Category Cable	Cat6 Cables

STANDARDS & COMPLIANCE

Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
--------------------	-------------------------------------

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	3-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.