

USB-C to DVI Adapter with Alternate Mode - DP 1.2, Black

MODEL NUMBER: U444-06N-DVIBAM



USB-C to DVI cable connects your DVI display to the USB-C or Thunderbolt 3 port on your laptop, MacBook or Chromebook.

Features

Connects a DVI Display to Your USB-C or Thunderbolt 3 Device This USB to DVI adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to a DVI-enabled television, monitor or projector. It's ideal for giving video presentations in conference rooms and classrooms, editing multiple documents on a larger screen or streaming video for digital signage in crystal-clear 1080p.

Supports USB DisplayPort Alternate Mode for Transmitting Video Signals With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

Transmits Crystal-Clear 1080p Video to a DVI Display To send high-definition video to a DVI television, projector or monitor, connect the DVI port to the display using a DVI cable (sold separately). The DVI port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz, 36-bit Deep Color (12 bits per channel) and DVI digital transfer rates up to 6.75 Gbps (2.25 Gbps per channel). The U444-06N-DVIBAM is also compatible with non-1080p DVI displays.

Built-In USB-C Cable Connects in Either Direction Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play Thunderbolt 3 and USB-C to DVI adapter requires no software, drivers or external power. It's about half the size of a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U444-06N-DVIBAM comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications.

Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

Applications

- Play 1080p video from your laptop or PC on a DVI display
- Give a video presentation at a meeting, training session, conference or trade show
- Multitask in two or more applications on multiple displays
- Add a second monitor and make it your primary monitor
- Edit large documents on two different monitors

System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with DVI input

Package Includes

- U444-06N-DVIBAM USB-C to DVI Adapter, USB 3.1, Thunderbolt 3, 1080p - M/F, Black
- Quick Start Guide

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332210708
Product Type	USB to DVI Adapter
Technology	DVI
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	DVI-I DUAL LINK (FEMALE)
Number of Monitors Supported	1
Video Ports	DVI-I DUAL LINK (FEMALE)
Video Ports Details	HDCP 1.3
Resolutions Supported	1920 x 1080 (1080p) @ 60 Hz
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p)
Max Supported Video Resolution	DVI: 1920 x 1080 (1080p) @ 60Hz
Mirror Mode	Yes
HDR Support	No
3D Video Supported	No
INPUT	
Built-In Cable Length (ft.)	0.33
Built-In Cable Length (m)	0.1
Built-In Cable Length (in.)	3.94
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Connector Plating	Nickel
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black
Material of Construction	PVC, ABS
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Number of Displays	1
Shipping Dimensions (hwd / in.)	0.80 x 3.80 x 4.80
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.570 x 1.800 x 1.700
Unit Packaging Type	Box
Unit Weight (lbs.)	0.05
Unit Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
HDCP Specification	1.2
Driver Required	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.