

Wall-Mounted Workstation, Single Display

MODEL NUMBER: **WWSS1332W**



Wall-mounted workstation transforms your desk space into an ergonomic sit-stand area without modifying the work surface.

Features

Enjoy the Benefits of Standing During Your Workday This sit-stand workstation mounts to the wall using the included hardware, allowing you to enjoy the benefits of better workplace ergonomics. Standing for part of the day can help increase metabolism, improve alertness and productivity, reduce fatigue and decrease the risk of repetitive stress injuries. Ideal for home, school or office use, the WWSS1332W lets you sit or stand with 19.5 inches of single-motion height extension.

Easy to Adjust to Your Liking With a Single Touch Just one touch is all it takes to adjust your wall-mounted workstation's angles and heights to fit your comfort level. All sections move together for smooth transitions between sitting and standing modes. The full-motion arm swivels from -90° to +90° to give you plenty of flexibility in minimizing glare and providing comfortable viewing. It also rotates 360 degrees for viewing in portrait or landscape orientation. Increase or decrease tension using the included hex key to compensate for heavier or lighter loads.

VESA-Compliant Mount Supports Up to 17.6 lb. The VESA-compliant single-arm mount fits most flat-panel monitors, televisions and other displays from 13 to 32 inches. It's compatible with 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm VESA mounting-hole patterns.

Extra-Large Keyboard Tray Holds the Most Popular Models The large keyboard tray, with soft padded wrist rest, measures 26.2 x 10.2 inches and flips up to save space when not in use. A secondary surface is ideal for telephones, fans and other desk accessories.

5-Year Warranty and Environmentally Responsible Design The WWSS1332W sit-stand workstation comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications.

Specifications

OVERVIEW	
UPC Code	037332212740
Device Compatibility	Monitor/HDTV; Computer; Laptop

Highlights

- Mounts firmly to wall to leave valuable desk or table space clear
- Adjusts to fit wide range of flat-screen monitors from 13 to 32 in.
- Keyboard tray with padded wrist rest flips up when not in use to conserve workspace
- Monitor swivels from -90° to +90° and rotates 360° to customize the ideal viewing angle
- Includes necessary mounting hardware so you can start installation immediately

Applications

- Transform your work area into a sit-stand environment to reap the health benefits of standing for part of your workday

Package Includes

- Bracket arm
- Support mast
- Keyboard shelf
- (2) Decorative covers
- Hex key, 4 mm
- Hex key, 6 mm
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black; Silver
Material of Construction	Steel, Plastic
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Motion	Full Motion/Rotate
Mounting Location	Wall
Degrees of Motion	180 swivel and 360 rotate
Minimum Screen Size (in.)	13
Minimum Screen Size (cm)	33.02
Maximum Screen Size (in.)	32
Maximum Screen Size (cm)	81.28
Maximum Weight Capacity (lbs.)	17.6
Maximum Weight Capacity (kg)	8
Number of Displays	1
Unit Dimensions (hwd / in.)	26.200 x 31.100 x 37.600
Unit Dimensions (hwd / cm)	66.548 x 78.994 x 95.504
Unit Weight (lbs.)	19.9
Unit Weight (kg)	9.03
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.