






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF AMPHENOL LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY AMPHENOL LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2013/11/07	Ann	New Item
B	C190315	2019/03/20	Ruru	Modify Note & Add QC Dimension


ALTW
CONFIDENTIAL
 2019-03-20
R&D DEPT.



Pin Assignments
Front View



Recommended Panel
Cut-Out




Note: B

- * ∅ Important Dimension
- * Waterproof Rate: IP67, Unmated
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Gray
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 2.8mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.0mm
- * Gasket and Nut are packed separately in PE bags

UNIT:mm

TOLERANCE	
.X	±0.25
.XX	±0.1
.XXX	±0.05
ANGLES	±1°



TITLE Standard CNC Pin Panel Lock 5Pin M Conn M Pin			
SCALE 2:1	SIZE A4	SHEET 1 OF 1	
REV. B	WC-REV. A.3	∅ : Inspection item	

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO IBD-05PMMS-LC7001	DWG NO IBD-05PMMS-LC7001	CUSTOMER ALTW
------------------------------	-----------------------------	------------------

DRAWN BY Ruru	CHECKED BY Rita	APPROVED BY Max
------------------	--------------------	--------------------

DATE 2019-03-20	DATE 2019-03-20	DATE 2019-03-20
--------------------	--------------------	--------------------