




THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION



Conn.




ICD-09AFFM-SL7AXX

- XX : 01~99Meters
- 01 : 01Meter
- 02 : 02Meters
- :
- 99 : 99Meters

Cable Length(L):01~99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Screw Nut: Nylon+GF, Black.
 - * O-Ring: Silicon, Gray
 - * Cable: UL2464 24AWG*9C+Drain+Al/My PVC Jacket UV Resistant, OD=6.0, Black.
 - * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm



Pin Assignments
Front View

9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn. Wire Color		
Pin Out		

UNIT:mm		TOLERANCE		TITLE		ITEM NO		DRAWN BY		DATE	
±0.5				MIDDLE CNC PIN CABLE SCREW 9P F CONN F PIN		ICD-09AFFM-SL7AXX		Jiazhen_Li		2014-01-10	
SCALE		SIZE		SHEET		DWG NO		CHECKED BY		DATE	
1:1		A4		1 OF 1		ICD-09AFFM-SL7AXX		Ruru		2014-01-10	
REV.		WC-REV.		QC:Inspection item		CUSTOMER		APPROVED BY		DATE	
A		A.2				ALTW		Jerry		2014-01-10	

Amphenol LTW
安費諾亮泰企業股份有限公司