



REV.	ECN NO.	DATE	SIGN	DESCRIPTION




ICD-09BFMM-LL6A XX

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
:
XX: 99Meters

Cable Length(L): 01~99Meters


Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP66
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Lock Nut: Nylon+GF. Black
- * O-Ring: Silicon, Gary.
- * Cable: UL2464 24AWG*9C+Drain+Al/My
PVC Jacket UV Resistant, OD=6.0, Black.
- * Cable Length Tolerance: 01M: 40mm
02M~05M: ± 60 mm
06M~10M: ± 100 mm
11M~30M: ± 200 mm
31M~99M: ± 500 mm



9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gary	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color	Pin Out

UNIT:mm
TOLERANCE ± 0.5



TITLE MIDDLE CNC PIN CABLE LOCK 9P F CONN M PIN			
SCALE 1:1	SIZE A4	SHEET 1 OF 1	
REV. A	WC-REV. A.2	$\varnothing$: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Lin_rensong	DATE 2013-11-29
DWG NO ICD-09BFMM-LL6AXX	CHECKED BY Tony_leng	DATE 2013-11-29
CUSTOMER ALTW	APPROVED BY Victor	DATE 2013-11-29