

**ICA12-50JPL**

1/2" Plenum-Rated Corrugated Coaxial Cable, 50 ohm, Up to 6GHz, Blue Color

ClearFill®Line Plenum-Rated 1/2" Air Dielectric Cable

RFS Technologies' 1/2" air dielectric cable is specifically engineered to meet stringent plenum requirements in both the United States and Canada, ensuring compliance with NEC and NFPA safety standards for use in air-handling spaces. Designed for exceptional RF performance and low loss, this cable is widely used in Distributed Antenna System (DAS) projects for in-building wireless communication, including commercial buildings, airports, hospitals, and other high-density venues. Its flexible construction allows for easy routing in tight plenum spaces, while its robust shielding ensures minimal signal interference. Ideal for applications requiring high signal integrity and regulatory compliance.

**FEATURES / BENEFITS**

1/2" Plenum-Rated DAS Cable

- **High-Frequency Performance up to 6 GHz.** Engineered to support RF signals across a broad frequency range—including up to 6 GHz—this cable meets the demands of today's advanced wireless communication systems, including 5G and future-ready networks.
- **Superior Shielding for Maximum Interference Protection.** The solid outer conductor provides complete 360° RFI/EMI shielding, significantly reducing signal leakage and minimizing system interference in high-density RF environments.
- **Exceptional Intermodulation Performance.** With both solid inner and outer conductors, the cable virtually eliminates passive intermodulation (PIM), ensuring clean signal transmission.
- **Optimized for Plenum-Space Installations.** Engineered to meet plenum-rated safety standards in the U.S. and Canada, this cable is ideal for indoor DAS applications in office buildings, hospitals, airports, and other public venues requiring strict fire safety compliance.

Technical features**APPLICATIONS**

Applications		Wireless Communication	Mobile Radio	In Building	DAS
--------------	--	------------------------	--------------	-------------	-----

STRUCTURE

Size		1/2
Inner Conductor Diameter	mm (in)	4.8 (0.19)
Inner Conductor Material		Copper-Clad Aluminum Wire
Dielectric Diameter	mm (in)	11.8 (0.464)
Dielectric Material		Extruded Polyethylene
Outer Conductor Diameter	mm (in)	13.8 (0.54)
Outer Conductor Material		Corrugated Copper
Jacket Diameter	mm (in)	15.93 (0.627)
Jacket Material		PVC, Plenum Rated / Color Blue
Cable Type		Air-Dielectric, Corrugated

**ICA12-50JPL**

1/2" Plenum-Rated Corrugated Coaxial Cable, 50 ohm, Up to 6GHz, Blue Color

TESTING AND ENVIRONMENTAL

Fire Performance		Flame Retardant, Plenum Rated
Flame Retardant Jacket Specifications		CMP (Communications Multipurpose Plenum)
Regulatory Compliance		NFPA 262 (UL910) / CATVP / CMP / UL444 / Canadian CSA C.22.2/FT6
Installation Temperature	°C(°F)	-20 to 60 (-4 to 140)
Storage Temperature	°C (°F)	-40 to 85 (-40 to 185)
Operation Temperature	°C(°F)	-40 to 85 (-40 to 185)

ELECTRICAL SPECIFICATIONS

Impedance	Ω	50 +/- 1
Maximum Frequency	GHz	6
Velocity	%	88
Capacitance	pF/m (pF/ft)	76 (23.2)
Inductance	μ H/m (μ H/ft)	0.19 (0.058)
Peak Power Rating	kW	40
RF Peak Voltage	Volts	2000
Jacket Spark	Volt RMS	8000
Inner Conductor dc Resistance	Ω /1000 m (Ω /1000 ft)	1.48 (0.45)
Outer Conductor dc Resistance	Ω /1000 m (Ω /1000 ft)	1.9 (0.58)
Return Loss (VSWR) Performance		24 (1.13) @ 698-960 MHz 24 (1.13) @ 1395-1432 MHz 24 (1.13) @ 1700-2155 MHz 20 (1.22) @ 2300-2700 MHz 18 (1.29) @ 3550-4200 MHz 18 (1.29) @ 5150-6000 MHz

MECHANICAL SPECIFICATIONS

Cable Weight, Nominal	kg/m (lb/ft)	0.246 (0.165)
Minimum Bending Radius, Single Bend	mm (in)	76 (3)
Minimum Bending Radius, Repeated Bends	mm (in)	127 (5)
Bending Moment	Nm (lb-ft)	4.1 (3)
Tensile Strength	N (lb)	1112 (250)
Recommended / Maximum Clamp Spacing	m (ft)	0.5 / 0.9 (1.8 / 3)
Crush Strength	kg/mm (lb/in)	1.964 (110)

**ICA12-50JPL**

1/2" Plenum-Rated Corrugated Coaxial Cable, 50 ohm, Up to 6GHz, Blue Color

ATTENUATION @ 20°C (68°F) AND POWER RATING @ 40°C (104°F)

Frequency, MHz	dB per 100m	dB per 100ft	Power, kW
0.5	0.15	0.05	40
1	0.21	0.06	34.30
1.5	0.26	0.08	27.90
2	0.30	0.09	24.20
10	0.67	0.20	10.70
20	0.95	0.29	7.55
30	1.17	0.36	6.15
50	1.52	0.47	4.74
88	2.04	0.62	3.53
100	2.18	0.67	3.30
108	2.27	0.69	3.17
150	2.70	0.82	2.67
174	2.92	0.89	2.47
200	3.14	0.96	2.30
300	3.89	1.19	1.85
400	4.54	1.39	1.59
450	4.84	1.48	1.49
500	5.13	1.56	1.41
512	5.19	1.58	1.39
600	5.66	1.73	1.28
700	6.16	1.88	1.17
750	6.40	1.95	1.13
800	6.64	2.02	1.09
824	6.75	2.06	1.07
894	7.06	2.15	1.02
900	7.08	2.16	1.02
925	7.19	2.19	1.01
960	7.34	2.24	0.99
1000	7.51	2.29	0.96
1250	8.52	2.60	0.85
1400	9.08	2.77	0.80
1500	9.45	2.88	0.77
1700	10.20	3.09	0.71
1800	10.50	3.20	0.69
2000	11.20	3.40	0.65
2100	11.50	3.50	0.63

**ICA12-50JPL**

1/2" Plenum-Rated Corrugated Coaxial Cable, 50 ohm, Up to 6GHz, Blue Color

2200	11.80	3.59	0.62
2300	12.10	3.69	0.60
2400	12.40	3.78	0.59
2500	12.70	3.87	0.58
2600	13	3.96	0.56
2700	13.30	4.05	0.55
3000	14.10	4.31	0.52
3500	15.50	4.73	0.47
3600	15.80	4.81	0.47
4000	16.80	5.13	0.44
4500	18.10	5.51	0.41
5000	19.30	5.88	0.38
5500	20.40	6.23	0.36
6000	21.60	6.58	0.34

Related Products

	Premium Connector		Standard C03 Connector		Standard C02 Connector	
Interface	Connector Model Number	Toolkit	Connector Model Number	Toolkit	Connector Model Number	Toolkit
N Male	NM-LCF12-D01	TRIM-SET-L12-D01	NM-LCF12-C03	TRIM-SET-L12-C02	NM-LCF12-C02-6	TRIM-SET-L12-C02
N Female	NF-LCF12-D01		NF-LCF12-C03		NF-LCF12-C02-6	
4.3-10 Male	43M-LCF12-D01		43M-LCF12-C03			
4.3-10 Female	43MFLCF12-D01		43F-LCF12-C03			
716 DIN Male	716M-LCF12-D01		716M-LCF12-C03			
716 DIN Female	716F-LCF12-D01		716F-LCF12-C03			

Other connector types are available upon request.

External Document Links[LINK TO VEX FILE](#)**Notes**