








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0554	2008/09/19	Shin	Add Note
C	LE3-940127	2009/03/24	LiuShuYun	Change Size 6.20mm to 6.2mm.
D	CI90274	2019/02/19	Ruru	Modify Note & Change Logo



Pin Assignments
Front View



Recommended Panel Cut-Out



Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Black

* Use with waterproof cap or dust cap
Panel Thickness Max: 4.0mm

* Use without waterproof cap or dust cap
Panel Thickness Max: 5.0mm

* Gasket and Nut are packed separately
in PE bags.

UNIT : mm			TITLE Panel Screw 2P M Conn M Pin		
TOLERANCE			SCALE	SIZE	SHEET OF
.X ±0.25			1:1	A4	1 OF 1
.XX ±0.1			REV.	WC-REV.	QC: Inspection item
.XXX ±0.05			D	A.4	
ANGLES					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	BB-02RMMS-SC7001	DRAWN BY	Ruru	DATE	2019-02-19
DWG NO	BB-02RMMS-SC7001	CHECKED BY	Rita	DATE	2019-02-19
CUSTOMER	ALTW	APPROVED BY	Max	DATE	2019-02-19