





F	1		2		3		4		5		6		7		8	
	REV.		ECN NO.		DATE		SIGN		DESCRIPTION							
	C		LEN15B0346~350		2015/11/07		Joyy		Add 7-8 And 9 Pin To The Common Drawing							
	D		C230222		2023/02/20		Ruru		△D X7							
E	E		C241281		2024/11/07		Ruru		△E X1							
D																
C																
B																
A																

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN15B0346~350	2015/11/07	Joyy	Add 7-8 And 9 Pin To The Common Drawing
D	C230222	2023/02/20	Ruru	△D X7
E	C241281	2024/11/07	Ruru	△E X1

</


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN15B0346~350	2015/11/07	Joyy	Add 7-8 And 9 Pin To The Common Drawing
D	C230222	2023/02/20	Ruru	△D X7
E	C241281	2024/11/07	Ruru	△E X1



△D
CD-XXAFFM-RL7AXX

XX: No. Of Pin

XX: 01~99Meters
01: 01Meter
02: 02Meters
:
99: 99Meters



Conn

Note: △D

- * RoHS Compliant
- * ∅ Important dimension
- * Waterproof rate: IP67, mated
- * Connector
- △C Housing: Thermoplastic, Black
- Pin: Copper Alloy, Gold Plated
- O-Ring: Rubber, Gray
- Outer mold: Thermoplastic, Black
- * Cable: UL2464, PVC Jacket, Black
- * Cable length tolerance: IM: +50/-0 mm
- 1M < L ≤ 3M: +100/-0 mm
- 3M < L ≤ 5M: +150/-0 mm
- 5M < L ≤ 10M: ±100 mm
- 10M < L ≤ 20M: ±200 mm
- 20M < L ≤ 30M: ±300 mm
- 30M < L ≤ 99M: ±500 mm
- * Prohibiting the use of place in oils

UNIT:mm			TITLE					
TOLERANCE ±0.5			RBL, C-5A, CABLE W/SR F, F, MOLDING, RBL 					
			SCALE	3:4	SIZE	A4	SHEET	1 OF 2
			REV.	E	WC-REV.	A.3	 : Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO		DRAWN BY		DATE	
		Ruru		2024-11-05	
DWG NO		CHECKED BY		DATE	
CD-XXAFFM-RL7AXX		Rita		2024-11-05	
CUSTOMER		APPROVED BY		DATE	
ALTW		Fred		2024-11-05	

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

