


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A4	NEW RELEASE	03/DEC/2021	
A5	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A6	CHANGE CABLE PRINTING	28/JULY/2025	



NOTE:

1. TESTING CONDITIONS:
 - A: INSULATION RESISTANCE: 10M Ω
 - B: VOLTAGE: DC300V/0.01S
 - C: CONDUCTOR RESISTANCE 2 Ω ($\leq 3M$), 5 Ω ($> 3M, < 10M$), 8M $\geq 10\Omega$
2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT			
P1	P2	P1	P2
1 ———	1 BLACK	9 ———	9 GREY
2 ———	2 BROWN	10 ———	10 WHITE
3 ———	3 RED	11 ———	11 PINK
4 ———	4 ORANGE	12 ———	12 LIGHT GREEN
5 ———	5 YELLOW	13 ———	13 BLACK/WHITE
6 ———	6 GREEN	14 ———	14 BROWN/WHITE
7 ———	7 BLUE	15 ———	15 RED/WHITE
8 ———	8 PURPLE	SHELL ———	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDHD15MF0-014IN	14"±1inch	356±25mm
CS-DSDHD15MF0-001.5	1.5FT±1inch	457±25mm
CS-DSDHD15MF0-002.5	2.5FT±1inch	762±25mm
CS-DSDHD15MF0-005	5FT±2inch	1524±51mm
CS-DSDHD15MF0-007.5	7.5FT±2inch	2286±51mm
CS-DSDHD15MF0-010	10FT±3inch	3048±76mm
CS-DSDHD15MF0-015	15FT±3inch	4572±76mm
CS-DSDHD15MF0-025	25FT±4inch	7620±102mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand		REV.	
DECIMALS ANGLES		APPROVALS		20 VALLEY ST. ENDICOTT, NY 13760		A6	
.X ±X ± X°		DRAWN XF		DELUXE HD15M/F MOLDED XFT			
.XX ±.XX		CHECKED HYJ					
.XXX ±.XXX		THIRD ANGLE PROJECTION		SIZE		DWG. NO.	
		RESP ENG		CS-DSHD15MF0-XXX			
		MFG ENG		A			
CAD FILE:				SCALE: N/A		SHEET 1 OF 1	

NOTES: UNLESS OTHERWISE SPECIFIED