






REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A5	NEW RELEASE	17/AUG/2022	
A6	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A7	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER



- NOTE:
- TESTING CONDITIONS:
A: INSULATION RESISTANCE: 10MΩ
B: VOLTAGE: DC300V/0.01S
C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
 - SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

P1	P2	P1	P2
1	1 BLACK	15	15 RED/WHITE
2	2 BROWN	16	16 ORANGE/WHITE
3	3 RED	17	17 GREEN/WHITE
4	4 ORANGE	18	18 BLUE/WHITE
5	5 YELLOW	19	19 PURPLE/WHITE
6	6 GREEN	20	20 RED/BLACK
7	7 BLUE	21	21 ORANGE/BLACK
8	8 PURPLE	22	22 YELLOW/BLACK
9	9 GREY	23	23 GREEN/BLACK
10	10 WHITE	24	24 GRAY/BLACK
11	11 PINK	25	25 PINK/BLACK
12	12 LIGHT GREEN	26	26 PINK/RED
13	13 BLACK/WHITE		
14	14 BROWN/WHITE	SHELL	SHELL DRAIN

P/N CHART

ACD P/N	LENGTH±T	
CS-DSDHD26MF0-001.6	1.6FT±1.0inch	488±25mm
CS-DSDHD26MF0-002.5	2.5FT±1inch	762±25mm
CS-DSDHD26MF0-005	5FT±2inch	1524±51mm
CS-DSDHD26MF0-010	10FT±3inch	3048±76mm
CS-DSDHD26MF0-015	15FT±3inch	4572±76mm
CS-DSDHD26MF0-025	25FT±4inch	7620±102mm
CS-DSDHD26MF0-050	50FT±8inch	15240±203mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	±.X	ANGLES	± X°		
.X	±.X			APPROVALS	DATE
.XX	±.XX			DRAWN	XF
.XXX	±.XXX			CHECKED	HYJ
THIRD ANGLE PROJECTION				RESP ENG	
				MFG ENG	
CAD FILE:		SIZE	DWG. NO.	REV.	
		A	CS-DSDHD26MF0-XXX	A7	
		SCALE: N/A		SHEET 1 OF 1	