


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A3	NEW RELEASE	22/June/2022	
A4	CHANGE CABLE PRINTING	28/JULY/2025	



NOTE:

1. TESTING CONDITIONS:
 - A: INSULATION RESISTANCE: 10MΩ
 - B: VOLTAGE: DC300V/0.01S
 - C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω
2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760				
DECIMALS .X .XX .XXX		APPROVALS DRAWN XF CHECKED HYJ					DATE	
ANGLES ±X° ±.XX ±.XXX		THIRD ANGLE PROJECTION 		RESP ENG		DELUXE, HD44 M/F MOLDED XX		
		MFG ENG						
CAD FILE				SIZE A	DWG. NO. CS-DSDHD44MFO-XXX		REV. A4	
				SCALE: N/A		SHEET 1 OF 1		

NOTES: UNLESS OTHERWISE SPECIFIED