


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	03/01/07	
A1	Add wiring color	16/JAN/2012	
A2	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
28AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 28AWG FT1 COPARTNER

NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω

2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

INNER LAYER CODE		OUTER LAYER CODE		OUTER LAYER CODE	
P1	P2	P1	P2	P1	P2
1	1 BLACK	20	20 BLACK	42	42 GREEN/BLACK
2	2 BROWN	21	21 BROWN	43	43 GREY/BLACK
3	3 RED	22	22 RED	44	44 PINK/BLACK
4	4 ORANGE	23	23 ORANGE	45	45 PINK/RED
5	5 YELLOW	24	24 YELLOW	46	46 PINK/BLUE
6	6 GREEN	25	25 GREEN	47	47 PINK/GREEN
7	7 BLUE	26	26 BLUE	48	48 LIGHT BLUE
8	8 PURPLE	27	27 PURPLE	49	49 LIGHT BLUE/BLACK
9	9 GREY	28	28 GREY	50	50 LIGHT BLUE/RED
10	10 WHITE	29	29 WHITE	51	51 LIGHT BLUE/BLUE
11	11 PINK	30	30 PINK	52	52 LIGHT BLUE/GREEN
12	12 LIGHT GREEN	31	31 LIGHT GREEN	53	53 GREY/RED
13	13 BLACK/WHITE	32	32 BLACK/WHITE	54	54 GREY/GREEN
14	14 BROWN/WHITE	33	33 BROWN/WHITE	55	55 PURPLE/BLACK
15	15 RED/WHITE	34	34 RED/WHITE	56	56 BLUE/BLACK
16	16 ORANGE/WHITE	35	35 ORANGE/WHITE	57	57 LIGHT GREEN/BLACK
17	17 GREEN/WHITE	36	36 GREEN/WHITE	58	58 LIGHT GREEN/RED
18	18 BLUE/WHITE	37	37 BLUE/WHITE	59	59 LIGHT GREEN/BLUE
19	19 PURPLE/WHITE	38	38 PURPLE/WHITE	60	60 LIGHT GREEN/GREEN
		39	39 RED/BLACK	61	61 LIGHT YELLOW
		40	40 ORANGE/BLACK	62	62 LIGHT YELLOW/BLACK
		41	41 YELLOW/BLACK		
				SHELL	SHELL DRAIN WIRE

P/N CHART


ACD P/N	LENGTH±T	
CS-DSDHD62MM0-002.5	2.5FT±1inch	762±25mm
CS-DSDHD62MM0-005	5FT±2inch	1524±51mm
CS-DSDHD62MM0-010	10FT±3inch	3048±76mm
CS-DSDHD62MM0-015	15FT±3inch	4572±76mm
CS-DSDHD62MM0-025	25FT±4inch	7620±102mm
CS-DSDHD62MM0-050	50FT±8inch	15240±203mm



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES
.X ±X	±X°
.XX ±XX	
.XXX ±XXX	

THIRD ANGLE PROJECTION



CAD FILE:

EAR NO.

APPROVALS

DATE

DRAWN

CHECKED

RESP ENG

MFG ENG

Amphenol Cables on Demand

20 VALLEY ST. ENDICOTT, NY 13760

ASM CBL Deluxe High Density
62PIN D-Sub MM

SIZE
A

DWG. NO.

CS-DSDHD62MM0-XXX

REV.
A2

NOTES: UNLESS OTHERWISE SPECIFIED

SCALE: N/A SHEET 1 OF 1