



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A5	NEW RELEASE	03/DEC/2021	
A6	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A7	CHANGE CABLE PRINTING	28/JULY/2025	


LENGTH±T





P1



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER



P2



NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω

2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°,
DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

P1	P2	P1	P2
1	1 BLACK	9	9 GREY
2	2 BROWN	10	10 WHITE
3	3 RED	11	11 PINK
4	4 ORANGE	12	12 LIGHT GREEN
5	5 YELLOW	13	13 BLACK/WHITE
6	6 GREEN	14	14 BROWN/WHITE
7	7 BLUE	15	15 RED/WHITE
8	8 PURPLE	SHELL	SHELL DRAIN

P/N CHART


ACD P/N	LENGTH±T	
CS-DSDMDB15FF-005	5FT±2inch	1524±51mm
CS-DSDMDB15FF-012	12FT±3inch	3660±76mm
CS-DSDMDB15FF-015	15FT±3inch	4572±76mm



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	ANGLES
.X ±X	± X°
.XX ±.XX	
.XXX ±.XXX	

THIRD ANGLE PROJECTION



EAR NO.

APPROVALS

DATE

DRAWN

XF

CHECKED

HYJ

RESP ENG

MFG ENG

Amphenol Cables on Demand

20 VALLEY ST. ENDICOTT, NY 13760

DELUXE DB15F/F MOLDED

SIZE
A

DWG. NO.

CS-DSDMDB15FF-XXX

REV.
A7

NOTES: UNLESS OTHERWISE SPECIFIED

CAD FILE:

SCALE: N/A

SHEET 1 OF 1