


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	23/APR/2007	
A1	Add 360° Copper Foil Shield	21/MAY/2007	
A2	Add wiring color	16/JAN/2012	



NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: $10M\Omega$

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE $2\Omega(\leq 3M)$, $5\Omega(> 3M, < 10M)$, $8\Omega(\geq 10M)$

2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

P/N	L±T	
CS-DSLSZH25MF-002.5	762±25mm	2.5FT±1inch
CS-DSLSZH25MF-005	1524±51mm	5FT±2inch
CS-DSLSZH25MF-010	3048±76mm	10FT±3inch
CS-DSLSZH25MF-015	4572±76mm	15FT±3inch
CS-DSLSZH25MF-025	7620±102mm	25FT±4inch
CS-DSLSZH25MF-050	15240±203mm	50FT±6inch
CS-DSLSZH25MF-125	38100±300mm	125FT±8inch

PIN OUT					
P1	P2		P1	P2	
1	1	BLACK	14	14	BROWN/WHITE
2	2	BROWN	15	15	RED/WHITE
3	3	RED	16	16	ORANGE/WHITE
4	4	ORANGE	17	17	GREEN/WHITE
5	5	YELLOW	18	18	BLUE/WHITE
6	6	GREEN	19	19	PURPLE/WHITE
7	7	BLUE	20	20	RED/BLACK
8	8	PURPLE	21	21	ORANGE/BLACK
9	9	GRAY	22	22	YELLOW/BLACK
10	10	WHITE	23	23	GREEN/BLACK
11	11	PINK	24	24	GRAY/BLACK
12	12	LIGHT GREEN	25	25	PINK/BLACK
13	13	BLACK/WHITE	SHELL		SHELL DRAIN WIRE

NOTES: UNLESS OTHERWISE SPECIFIED



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	APPROVALS	DATE		
X ±X	±X°	DRAWN LF	16/JAN/2012	LSZH Data Cable 25 PIN D-Sub MF	
.XX ±XX		CHECKED BA	16/JAN/2012		
.XXX ±XXX		RESP ENG		SIZE A DWG. NO. CS-DSLSZH25MF-XXX REV. A2	
THIRD ANGLE PROJECTION		MFG ENG			
CAD FILE				SCALE: N/A SHEET 1 OF 1	