


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	23/APR/2007	
A1	Add 360° Copper Foil Shield	21/MAY/2007	
A2	Add wiring color	16/JAN/2012	

L±T

4-40THREAD(UNC)
4X THUMBSCREW



CABLE PRINTING: Amphenol Cables on Demand E119932 AWM 21118 80°C 30V COPARTNER



NOTE:

- 1. TESTING CONDITIONS:
 - A: INSULATION RESISTANCE: 10MΩ
 - B: VOLTAGE: DC300V/0.01S
 - C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M),8Ω(≥10M)
- 2. SHIELDING:COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

P/N	L±T	
CS-DSLSZH25MM-002.5	762±25mm	2.5FT±1inch
CS-DSLSZH25MM-005	1524±51mm	5FT±2inch
CS-DSLSZH25MM-010	3048±76mm	10FT±3inch
CS-DSLSZH25MM-015	4572±76mm	15FT±3inch
CS-DSLSZH25MM-025	7620±102mm	25FT±4inch
CS-DSLSZH25MM-050	15240±203mm	50FT±6inch
CS-DSLSZH25MM-125	38100±300mm	125FT±8inch

PIN OUT			
P1	P2	P1	P2
1	1 BLACK	14	14 BROWN/WHITE
2	2 BROWN	15	15 RED/WHITE
3	3 RED	16	16 ORANGE/WHITE
4	4 ORANGE	17	17 GREEN/WHITE
5	5 YELLOW	18	18 BLUE/WHITE
6	6 GREEN	19	19 PURPLE/WHITE
7	7 BLUE	20	20 RED/BLACK
8	8 PURPLE	21	21 ORANGE/BLACK
9	9 GRAY	22	22 YELLOW/BLACK
10	10 WHITE	23	23 GREEN/BLACK
11	11 PINK	24	24 GRAY/BLACK
12	12 LIGHT GREEN	25	25 PINK/BLACK
13	13 BLACK/WHITE	SHELL	SHELL DRAIN WIRE



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
DECIMALS ±X ANGLES ±X°
X ±X
.XX ±.XX
XXX ±.XXX

THIRD ANGLE PROJECTION

APPROVALS
DRAWN: HYJ
CHECKED: XF
RESP ENG
MFG ENG

EAR NO.

Amphenol Cables on Demand
20 VALLEY ST. ENDICOTT, NY 13760

LSZH Data Cable 25 PIN D-Sub MM

SIZE A DWG. NO. CS-DSLSZH25MM-XXX

REV. A2

CAD FILE

SCALE: N/A SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED