


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A3	NEW RELEASE	03/DEC/2021	
A4	Correct the misspellings of bubble and length on page 2	06/DEC/2022	



PIN OUT	
P1	P2
1	1 BLACK
2	2 BROWN
3	3 RED
4	4 ORANGE
5	5 YELLOW
6	6 GREEN
7	7 BLUE
8	8 PURPLE
9	9 GREY
SHELL	SHELL DRAIN

NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(<=3M), 5Ω(>3M,<10M), 8MΩ(>10M)

2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART


ACD P/N	LENGTH ± T	
CS-DSLSZH9MF0-002.5	2.5FT±1inch	762±25mm
CS-DSLSZH9MF0-005	5FT±2inch	1524±51mm
CS-DSLSZH9MF0-010	10FT±3inch	3048±76mm
CS-DSLSZH9MF0-015	15FT±3inch	4572±76mm
CS-DSLSZH9MF0-025	25FT±4inch	7620±102mm
CS-DSLSZH9MF0-050	50FT±4inch	15240±102mm
CS-DSLSZH9MF0-125	125FT±8inch	38100±203mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	ANGLES
.X ±X	±X°
.XX ±.XX	
.XXX ±.XXX	

THIRD ANGLE PROJECTION



CAD FILE:

EAR NO.

APPROVALS	DATE
DRAWN XF	
CHECKED HYJ	
RESP ENG	
MFG ENG	

Amphenol Cables on Demand

20 VALLEY ST. ENDICOTT, NY 13760

CABLE, 9PIN D-SUB M/F LSOH XFT

SIZE	DWG. NO.	REV.
A	CS-DSLSZH9MF0-XXX	A4

NOTES: UNLESS OTHERWISE SPECIFIED

SCALE: N/A SHEET 1 OF 1