


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.




REV.		REVISIONS	
REV.	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE	02/APR/2007	
A1	Add wiring color	16/JAN/2012	

LENGTH



D-SUB
25PIN Male

D-SUB
9PIN Female



PIN OUT:

DB25-M	DB9-F	COLOR
PIN2	PIN2	Brown
PIN3	PIN3	Red
PIN4	PIN8	Orange
PIN5	PIN7	Black
PIN7	PIN5	Green
PIN6	PIN4	Yellow & Gray
PIN8		
PIN20	PIN1	Blue
PIN1	PIN6	Purple
SHIELD	SHIELD	Drain Wire

LENGTH & P/N Table

LENGTH	P/N	Cable Color
5FT ±2 Inch	CS-DSNL4259MF-005	GREY
10FT ±3 Inch	CS-DSNL4259MF-010	GREY
25FT ±4 Inch	CS-DSNL4259MF-025	GREY



NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760					
DECIMALS	ANGLES	APPROVALS	DATE	Null Modem DB25M/DB9F					
.X	±X°	DRAWN	LF						
.XX	±XX°	CHECKED	BA						
.XXX	±XXX°	RESP ENG							
THIRD ANGLE PROJECTION									
		MFG ENG		SIZE		DWG. NO.			
				A		CS-DSNL4259MF-XXX			
						SCALE	SHEET	OF	REV.
									A1