


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

| REVISIONS |                                                         |              |          |
|-----------|---------------------------------------------------------|--------------|----------|
| REV.      | DESCRIPTION                                             | DATE         | APPROVED |
| A2        | NEW RELEASE                                             | 22/NOV/2022  |          |
| A3        | Correct the misspellings of bubble and length on page 2 | 06/DEC/2022  |          |
| A4        | CHANGE CABLE PRINTING                                   | 28/JULY/2025 |          |



NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω

2. SHIELDING: METAL CAN SHIELD, DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT

| P1 | P2             | P1    | P2              |
|----|----------------|-------|-----------------|
| 1  | 1 BLACK        | 14    | 14 BROWN/WHITE  |
| 2  | 2 BROWN        | 15    | 15 RED/WHITE    |
| 3  | 3 RED          | 16    | 16 ORANGE/WHITE |
| 4  | 4 ORANGE       | 17    | 17 GREEN/WHITE  |
| 5  | 5 YELLOW       | 18    | 18 BLUE/WHITE   |
| 6  | 6 GREEN        | 19    | 19 PURPLE/WHITE |
| 7  | 7 BLUE         | 20    | 20 RED/BLACK    |
| 8  | 8 PURPLE       | 21    | 21 ORANGE/BLACK |
| 9  | 9 GREY         | 22    | 22 YELLOW/BLACK |
| 10 | 10 WHITE       | 23    | 23 GREEN/BLACK  |
| 11 | 11 PINK        | 24    | 24 GRAY/BLACK   |
| 12 | 12 LIGHT GREEN | 25    | 25 PINK/BLACK   |
| 13 | 13 BLACK/WHITE | SHELL | SHELL DRAIN     |

P/N CHART

| ACD P/N             | LENGTH±T    |             |
|---------------------|-------------|-------------|
| CS-DSPMDB25MM-001.5 | 1.5FT±1inch | 457±25mm    |
| CS-DSPMDB25MM-002.5 | 2.5FT±1inch | 762±25mm    |
| CS-DSPMDB25MM-005   | 5FT±2inch   | 1524±51mm   |
| CS-DSPMDB25MM-010   | 10FT±3inch  | 3048±76mm   |
| CS-DSPMDB25MM-015   | 15FT±3inch  | 4572±76mm   |
| CS-DSPMDB25MM-025   | 25FT±4inch  | 7620±102mm  |
| CS-DSPMDB25MM-050   | 50FT±8inch  | 15240±203mm |



|                                                                           |        |           |      |                                                               |                   |
|---------------------------------------------------------------------------|--------|-----------|------|---------------------------------------------------------------|-------------------|
| UNLESS OTHERWISE SPECIFIED<br>DIMENSIONS ARE IN INCHES<br>TOLERANCES ARE: |        | EAR NO.   |      | Amphenol Cables on Demand<br>20 VALLEY ST. ENDICOTT, NY 13760 |                   |
| DECIMALS                                                                  | ANGLES | APPROVALS | DATE | CABLE, DB25 M/M DBL SHLD                                      |                   |
| .X ±X                                                                     | ±X°    | DRAWN     |      |                                                               |                   |
| .XX ±XX                                                                   |        | CHECKED   |      |                                                               |                   |
| .XXX ±XXX                                                                 |        | RESP ENG  |      |                                                               |                   |
| THIRD ANGLE PROJECTION                                                    |        | MFG ENG   |      | SIZE                                                          | DWG. NO.          |
|                                                                           |        |           |      | A                                                             | CS-DSPMDB25MM-XXX |
| CAD FILE:                                                                 |        |           |      | SCALE: N/A                                                    | REV. A4           |
|                                                                           |        |           |      | SHEET 1                                                       | OF 1              |

NOTES: UNLESS OTHERWISE SPECIFIED