


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A2	NEW RELEASE	08/AUG/2022	
A3	Correct the misspellings of bubble and length on page 2	06/DEC/2022	
A4	ADDED LENGTH 5FT	15/MAY/2023	
A5	CHANGE CABLE PRINTING	28/JULY/2025	

LENGTH±T



## NOTE:

- TESTING CONDITIONS:
  - INSULATION RESISTANCE:  $10M\Omega$
  - VOLTAGE: DC300V/0.01S
  - CONDUCTOR RESISTANCE  $2\Omega(\leq 3M)$ ,  $5\Omega(>3M, <10M)$ ,  $8M\geq 10\Omega$
- SHIELDING: METAL CAN SHIELD, DRAIN WIRE SOLDER TO CONNECTOR SHELL

## PIN OUT

P1	P2	P1	P2
1	1 BLACK	9	9 GREY
2	2 BROWN	10	10 WHITE
3	3 RED	11	11 PINK
4	4 ORANGE	12	12 LIGHT GREEN
5	5 YELLOW	13	13 BLACK/WHITE
6	6 GREEN	14	14 BROWN/WHITE
7	7 BLUE	15	15 RED/WHITE
8	8 PURPLE	SHELL	SHELL DRAIN



## P/N CHART

ACD P/N	LENGTH±T
CS-DSPMHD15MM-002.5	2.5FT±1inch
CS-DSPMHD15MM-005	5.0FT±2inch
CS-DSPMHD15MM-006	6.0FT±2inch
CS-DSPMHD15MM-010	10FT±3inch
CS-DSPMHD15MM-012	12FT±3inch
CS-DSPMHD15MM-015	15FT±3inch
CS-DSPMHD15MM-025	25FT±4inch
	762±25mm
	1524±51mm
	1829±51mm
	3048±76mm
	3657±76mm
	4572±76mm
	7620±102mm

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		EAR NO.	Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS	ANGLES	APPROVALS	DATE	
X	±X	DRAWN	XF	CABLE, HD15M/M DBL SHLD
XX	±XX	CHECKED	HYJ	
XXX	±XXX	THIRD ANGLE PROJECTION	RESP ENG	
		MFG ENG		SIZE DWG. NO. REV.
				A CS-DSPMHD15MM-XXX A5
CAD FILE:			SCALE: N/A	1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED