






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

B

A



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80° C 300V
26AWG VW-1 LL84201 CSA AWM I/II A 80° C 300V 26AWG FT1 COPARTNER



NOTE:

1. TESTING CONDITIONS:

A: INSULATION RESISTANCE: 10MΩ

B: VOLTAGE: DC300V/0.01S

C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8Ω(≥10M)

2. SHIELDING:AL-FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

PIN OUT			
P1	P2	P1	P2
1	1 BLACK	14	14 BROWN/WHITE
2	2 BROWN	15	15 RED/WHITE
3	3 RED	16	16 ORANGE/WHITE
4	4 ORANGE	17	17 GREEN/WHITE
5	5 YELLOW	18	18 BLUE/WHITE
6	6 GREEN	19	19 PURPLE/WHITE
7	7 BLUE	20	20 RED/BLACK
8	8 PURPLE	21	21 ORANGE/BLACK
9	9 GRAY	22	22 YELLOW/BLACK
10	10 WHITE	23	23 GREEN/BLACK
11	11 PINK	24	24 GRAY/BLACK
12	12 LIGHT GREEN	25	25 PINK/BLACK
13	13 BLACK/WHITE	SHELL	SHELL DRAIN WIRE



P/N CHART

ACD P/N	L±T	
CS-DSSMDB25MF-002.5	762±25mm	2.5FT ±1 inch
CS-DSSMDB25MF-005	1524±51mm	5FT ±2 inch
CS-DSSMDB25MF-010	3048±76mm	10FT ±3 inch
CS-DSSMDB25MF-015	4572±76mm	15FT ±3 inch
CS-DSSMDB25MF-025	7620±102mm	25FT ±4 inch
CS-DSSMDB25MF-050	15240±203mm	50FT ±8 inch

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMALS .X ±X .XX ±.XX .XXX ±.XXX ANGLES ±X° THIRD ANGLE PROJECTION 		EAR NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
		A'PROVALS	DATE	Economy 25PIN D-Sub MF Common Serial Connection	
		DRAWN XF			
		CHECKED HYJ			
RESP ENG		MFG ENG		SIZE A	DWG. NO. CS-DSSMDB25MF-XXX
CAD FILE				SCALE: N/A	SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED