




Cable Length(L):01~99Meters



DCU-08AFDM-LL7000



Conn.
Pin Assignments
Front View

8	Brown	16AWG	棕
7	Green/Yellow	16AWG	綠 / 黃
6	Blue	16AWG	藍
5	Red	24AWG	紅
4	Green	24AWG	綠
3	White	24AWG	白
2	Blue	24AWG	藍
1	Drain		地線
Conn.	Wire Color		
	Pin Out		

Note:

- NOTE: Important Dimension To Check
- * Waterproof Rate: IP67
 - * Connector: Nylon+GF, UL94V-0, Black
 - * Pin: Copper Alloy, Gold Plated
 - * O-Ring: Silicone, Gray
 - * Lock Nut: Nylon+GF, Black
 - * Cable: UL2586 (24#*1P+A)*2C+16#*3C+Drain+AI/Mylar, PVC Jacket, UV Resistant, OD=Ø10.0mm, Black
 - * Cable Length Tolerance: 01M±40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

UNIT:mm				TITLE O CERES, D-20A+2A, 08P, CABLE W/SR F, F PWR+M SIG, MOLDING, 2LOCK 				Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Ruru		DATE 2024-05-24			
TOLERANCE ± 0.5 mm 				SCALE 1:1		SIZE A4				SHEET 1 OF 1		DWG NO DCU-08AFDM-LL7BXX		CHECKED BY Rita		DATE 2024-05-24	
				REV. C		WC-REV. B.2				QC: Inspection item		CUSTOMER ALTW		APPROVED BY Fred		DATE 2024-05-24	