

Technical data sheet

Stainless Steel Hygienic Fittings for Food and Beverage Applications

LUTZE FBP FITTINGS



Identification

Type FBP Fitting M20
Part No. [FHM20](#)

Product version

Datasheet version 00

Use/Application/Properties

Properties	• Designed for the demanding requirements of food, beverage, and drug processing applications • Made with food contact approved materials in conformance with 21 CFR 177.2600 • Smooth finish prevents microbial build-up • IP69 high-pressure washdown resistance • Integrated strain relief • Wide sealing and clamping range • Adapts to different size cable shields • 360° shield termination • Contact spring made of special copper alloy providing low contact resistance
------------	---

Technical data

Clamping range D	6 mm – 12 mm
Clamping range D	0.236 inch – 0.472 inch
Temperature range	-20 °C ... +100 °C -4 °F ... +212 °F
Intermittent temperature range	-40 °C ... +150 °C -40 °F ... +302 °F
Degree of protection	Type 4X UL50E IP69 EN 60529
Thread form	metric
Thread standard	metric acc. to EN 60423
Thread G	M20×1.5
TL	8 mm
H	29.5 mm

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

05.09.2022 • Subject to technical modification

Part No. [FHM20](#) • Datasheet version: 00

page 1 of 2

Technical data sheet

Stainless Steel Hygienic Fittings for Food and Beverage Applications

SWC	22 mm
SWB	13 mm

Construction

Material	Steel, stainless EN 1.4305 / AISI 303
Material seal	EPDM
Material clamping insert	POM
Material contact spring	Special copper alloy

Approvals/Standards

Approvals	cULus
-----------	-------

Dimensions

