

Technical data sheet

Cable fittings and accessories



Identification

Type	TOP-T Metal M50×1.5
Part No.	FMM50

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Properties	• Integrated strain relief • Anti-twist design • Wide sealing and clamping range • Easy to install
------------	--

Technical data

Clamping range D	22 mm – 32 mm
Clamping range D	0.866 inch – 1.26 inch
Temperature range	-20 °C ... +100 °C -4 °F ... +212 °F
Intermittent temperature range	-40 °C ... +150 °C -40 °F ... +302 °F
Protection class	IP68
Thread form	metric
Thread standard	metric acc. to EN 60423
Thread G	M 50×1.5
SW 1	50 mm
SW 2	55 mm
TL	9 mm
H	48 mm

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

Technical data sheet

Cable fittings and accessories

Construction

Material	Brass nickel-plated
Material seal	CR chloroprene rubber
Material O-ring	NBR
Material clamping insert	PA 6
Surface	nickel-plated

Certifications/Standards

Certifications	cULus
----------------	-------

Notes and Comments

Note	Locknuts sold separately
------	--------------------------

Dimensions

