

Technical data sheet

Cable fittings and accessories



Identification

Type	TOP-T EMC Metal NPT 2 1/2"
Part No.	FMNPT212-CEX

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Properties	• Designed for large diameter cables • Two seal inserts for clamping range adjustment • Adapts to different size cable shields • 360° shield termination • Integrated strain relief • Wide sealing and clamping range • Fast and easy to install
------------	--

Technical data

Clamping range D	46 mm – 62 mm
Clamping range D	1.812 inch – 2.44 inch
Temperature range	-20 °C ... +100 °C -4 °F ... +212 °F
Intermittent temperature range	-40 °C ... +150 °C -40 °F ... +302 °F
Protection class	IP68
Thread form	NPT
Thread standard	per ANSI ASME B1.21.1
Thread G	NPT 2 1/2"
SW 1	80 mm
SW 2	80 mm
TL	21 mm

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

02.12.2021 • Subject to technical modification

Part No. FMNPT212-CEX • Datasheet version: 00

page 1 of 2

Technical data sheet

Cable fittings and accessories

H 55 mm

Construction

Material	Brass nickel-plated
Material seal	CR chloroprene rubber
Material O-ring	NBR
Material clamping insert	PA 6
Surface	nickel-plated

Certifications/Standards

Certifications cULus

Notes and Comments

Note Locknuts sold separately

Dimensions

