

Technical data sheet

Cable fittings and accessories

LUTZE TOP-T Fittings Metric Plastic metric



Identification

Type	TOP-T Plastic M20×1,5
Part No.	FPM20B

Product version

Datasheet version	00
-------------------	----

Use/Application/Properties

Properties	• Integrated strain relief • Wide sealing and clamping range • Easy to install • manufactured acc. to EN 62444
------------	--

Technical data

Clamping range D	10 mm – 14 mm
Clamping range D	0.315 inch – 0.551 inch
Temperature range	-20 °C ... +100 °C -4 °F ... +212 °F
Intermittent temperature range	-40 °C ... +150 °C -40 °F ... +302 °F
Degree of protection	IP68
Diameter D	27 mm
Thread form	metric
Thread standard	metric acc. to EN 60423
Thread G	M20×1.5
TL	10 mm
TD	20 mm
H	31 mm

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk

Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)
www.luetze.de • info@luetze.de

18.04.2023 • Subject to technical modification

Part No. [FPM20B](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

Technical data sheet

Cable fittings and accessories

Construction

Material	PA 6
Material seal	CR chloroprene rubber
Color	schwarz ähnlich RAL 9005

General

PU (units)	50
------------	----

Certifications/Standards

Certifications	cULus
----------------	-------

Notes and Comments

Note	Locknuts sold separately
------	--------------------------

Dimensions

