

## Technical data sheet

### Cable fittings and accessories

#### LUTZE TOP-T Fittings PG Plastic PG



#### Identification

|          |                         |
|----------|-------------------------|
| Type     | TOP-T Plastic PG42      |
| Part No. | <a href="#">FPPG42G</a> |

#### Product version

|                   |    |
|-------------------|----|
| Datasheet version | 00 |
|-------------------|----|

#### Use/Application/Properties

|            |                                                                                                                                                                                        |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Properties | <ul style="list-style-type: none"><li>• Integrated strain relief</li><li>• Wide sealing and clamping range</li><li>• Easy to install</li><li>• manufactured acc. to EN 62444</li></ul> |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

#### Technical data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Clamping range D               | 30 mm – 38 mm                            |
| Clamping range D               | 1.181 inch – 1.496 inch                  |
| Temperature range              | -20 °C ... +100 °C<br>-4 °F ... +212 °F  |
| Intermittent temperature range | -40 °C ... +150 °C<br>-40 °F ... +302 °F |
| Degree of protection           | IP68                                     |
| Diameter D                     | 60 mm                                    |
| Thread form                    | PG                                       |
| Thread standard                | PG according DIN 40430                   |
| Thread G                       | PG 42                                    |
| TL                             | 13 mm                                    |
| TD                             | 54 mm                                    |
| H                              | 53.5 mm                                  |

#### United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park  
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU  
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2  
[www.lutze.com](http://www.lutze.com) • [sales.gb@lutze.co.uk](mailto:sales.gb@lutze.co.uk)

#### Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt  
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)  
[www.luetze.de](http://www.luetze.de) • [info@luetze.de](mailto:info@luetze.de)

18.04.2023 • Subject to technical modification

Part No. [FPPG42G](#) • Datasheet version: 00

page 1 of 2



SYSTEMATIC TECHNOLOGY

## Technical data sheet

### Cable fittings and accessories

#### Construction

|               |                                 |
|---------------|---------------------------------|
| Material      | PA 6                            |
| Material seal | CR chloroprene rubber           |
| Color         | silver grey similar to RAL 7001 |

#### General

|            |   |
|------------|---|
| PU (units) | 5 |
|------------|---|

#### Certifications/Standards

|                |       |
|----------------|-------|
| Certifications | cULus |
|----------------|-------|

#### Notes and Comments

|      |                          |
|------|--------------------------|
| Note | Locknuts sold separately |
|------|--------------------------|

#### Dimensions

