





				REV.	ECN NO.	DATE	SIGN	DESCRIPTION	
				B	C210561	2021/04/09	Vicky	△B X4	
				C	C221953	2022/12/15	Ruru	△C X1	
				D	C251612	2025/12/12	Vicky	△D X1	









3P




4P



5P




6P



8P

Pin Assignments Front View

UNIT:mm



TOLERANCE

.X ±0.25

.XX ±0.1

.XXX ±0.05

ANGLES ±1°

SCALE

1:1

SIZE

A4

SHEET

1

OF

1

REV.

D

WC-REV.

A.5

QC

Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

CUSTOMER

DRAWN BY

CHECKED BY

APPROVED BY

DATE

DATE

DATE

△B Note:

* RoHS Compliant

*  Important Dimension

△C * Waterproof rate: IP68, mated 1m/24h

* Connector

Housing: Thermoplastic, Black

Pin: Copper alloy, Gold plated

Extension Nut: Thermoplastic, Black

Nut: Metal

O-Ring: Rubber, Gray

* Gasket: Rubber, Gray

* Clamp Ring: Thermoplastic, Black

* Sealing Nut: Thermoplastic, Black

* Seal: Rubber, Gray, OD:Ø4.5mm~Ø6.5mm

△D * The Connector Is Not Assembled, And The Parts Are Packed In A Bag

△B M12A-XXBFFA-SL8001

XX: No. Of Pin

8

W10814-03-BM01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.