





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C210561	2021/04/09	Vicky	 X4
C	C221953	2022/12/15	Ruru	 X1
D	C251612	2025/12/12	Vicky	 X1



MI2A-XXBMA-SL800I
XX: No. Of Pin



Pin Assignments Front View

- Note:
- * RoHS Compliant
 - *  Important Dimension
 - *  Waterproof rate: IP68, mated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Extension Nut: Thermoplastic, Black
 - Nut: Metal
 - * Gasket: Rubber, Gray
 - * Clamp Ring: Thermoplastic, Black
 - * Sealing Nut: Thermoplastic, Black
 - * Seal: Rubber, Gray, OD: $\varnothing 4.5\text{mm} \sim \varnothing 6.5\text{mm}$
 - *  The Connector Is Not Assembled, And The Parts Are Packed In A Bag

UNIT : mm				TITLE N SEN, M12 A, SCREW CABLE W/O SR, M, M, FI SOLDER					Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Vicky		DATE 2025-12-12		
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±				SCALE 1 : 1		SIZE A4		SHEET 1 OF 1			DWG NO M12A-XXBMA-SL8001		CHECKED BY Ruru		DATE 2025-12-12		
REV. D		WC-REV. .0		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Rita			DATE 2025-12-12						