










REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	C210309	2021/02/26	Ruru	 X2
F	C221923	2022/12/06	Na Liu	 X3
G	C251374	2025/10/27	Vicky	 X1



Note: 

- * RoHS Compliant
- *  Important dimension
- *  Waterproof rate: IP67, mated
- *  Connector

Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
O-Ring: Rubber, Black

- *  Shield: Metal
- *  Nut: Metal
- *  O-Ring: Rubber, Gray
- * For panel thickness max: 3.0mm
- * For pcb thickness max: 1.6mm
- *  The Nut Is Packed Separately In The Bag

UNIT:mm				TITLE N SEN, M12 B, SCREW RECEPTACLE, M, M, PCB R		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Vicky		DATE 2025-10-27			
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 3:2		SIZE A4				SHEET 1 OF 1		DWG NO M12B-XXPMMR-SF7003		CHECKED BY Ruru		DATE 2025-10-27	
REV. G		WC-REV. A.1		QC-Inspection item				CUSTOMER ALTW		APPROVED BY Rita		DATE 2025-10-27			