


F	1		2		3		4		5		6		7		8		
									REV.	ECN NO.		DATE		SIGN		DESCRIPTION	
									A			2024/03/20		Eagle		Rev.01 to Rev.A	
									B	C251505		2025/11/18		Vicky		△B X2	
E																	
									Note:								
									* RoHS Compliant								
									* △ Important dimension								
D									* Waterproof rate: IP68, mated 1m/24h IP69K, mated								
									* Connector								
									Housing: Thermoplastic, Black								
									Pin: Copper alloy, Gold plated								
C									Nut: Metal								
									Outer mold: Thermoplastic, Black								
									* Cable: UL20234, 14#*5C, OD=10mm, TPU Jacket, Black								
									* Cable length tolerance: 1M: +50/-0 mm								
B									1M < L ≤ 3M: +100/-0 mm								
									3M < L ≤ 5M: +150/-0 mm								
									5M < L ≤ 10M: ±100 mm								
									10M < L ≤ 20M: ±200 mm								
A									20M < L ≤ 30M: ±300 mm								
									30M < L ≤ 99M: ±500 mm								

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.